



Step depths referenced to front of septum plate
 Step heights referenced to bottom of septum plate
 Prototype outer tube diameter 26mm
 Note - dimensions shown for septum plate do not include additional material for fixing - active dimensions only given
 For coax feeding, probe position is 16mm forward of rear plate
 Septum plate thickness 0.5mm

3cm CWST Septum Dimensions

G4HUP

Derived from OK1DFC spreadsheet

Dimensions in mm Scale 2:1
 Drawn by D Powis Version 0.A
 Date: 26 Aug 2010

